


Technology that saves lives

Genesis LED EGC Series

Ceiling Mount Notification Devices



Overview

Genesis LED EGC Series horns and LED strobes feature a sleek low profile design and energy-efficient technology that makes them less expensive to install and operate by reducing overhead. High performance LEDs require fewer power supplies, backup power, and batteries. These new appliances are designed with, energy-efficiency, and life safety in mind.

Genesis LED EGC Series uses high efficiency optics, combined with patented electronics, to deliver a highly controlled and efficiently focused light distribution pattern in exchange for lower current requirements. Strobes feature field-selectable 15, 30,75, or 115 cd light output.

Compared with Xenon-type strobes, Genesis LED EGC Series appliances need fewer power supplies and often smaller wire gauge, which lightens conduit requirements. They are also backwards compatible with legacy strobes, so there's no need to replace all your existing devices to upgrade to new LED technology. In fact, EGC strobes can be mixed on the same circuit and used in the same field of view as Xenon-based strobes. This makes Genesis LED EGC Series ideal for new installations and retrofits alike.

Field-configurable sound output levels provide the flexibility modern life safety projects demand, while the Genesis LED control protocol keeps multiple strobes on compatible NAC circuits synchronized to well within NFPA 72 requirements.

Serviceability is another area where EGC Series appliances shine. The universal room side wiring plate allows for pre-installation and electrical wiring as well as checking continuity with the included diagnostics check bar. EGC Series devices can then be easily snapped into place with the confidence of knowing the wiring is correct. The innovative under-cover diagnostic test points provide easy access to device circuit testing while mounted.

Standard Features

High Performance LED Strobe Technology

- Ultra low device current consumption allows:
 - More devices per circuit
- Ability to use lower gauge wire
- Longer wire runs
- Fewer booster power supplies
- High efficiency optics
- Selectable 15, 30, 75, or 115 cd light output
- LED devices may be mixed with legacy Xenon strobes

Efficient Audible Output

- Selectable high or low dB horn output
- Selectable temporal or steady horn output
- Improved audio frequency range for better wall penetration

Low-profile Design

- Ultra-slim... protrudes about 1.5" from the mounting surface
- Attractive appearance... no visible mounting screws

Multiple Marking Options

- Order Red or White with or without FIRE markings
- Change markings at any time with replaceable quick-swap covers

Easy to Install

- Pre-install and pre-wire with convenient universal room side wiring plate
- Check electrical continuity on room side wiring plate with included diagnostics check bar
- Diagnostics port streamlines device circuit testing
- Fits 1-gang, 2-gang, 4-inch octagon, and 4-inch square electrical boxes
- Optional red and white trim plates available
- Slide switches for field configuration
- $-\,$ 12 to 18 AWG in-out screw terminals for quick wiring

Application

Genesis EGC Series strobes are UL 1971-listed for use indoors as ceiling-mounted public-mode notification appliances for the hearing impaired. Prevailing codes require strobes to be used where ambient noise conditions exceed 105 dBA (87 dBA in Canada), where occupants use hearing protection, and in areas of public accommodation as defined in the Americans with Disabilities Act.

Synchronization is important in order to avoid triggering seizures in people with photosensitive epilepsy. All Genesis strobes exceed UL synchronization requirements (within 10 milliseconds over a two-hour period) when used with a synchronization source. See the specifications table for a list of compatible sources.

Horns


Genesis horn output reaches as high as 92 dBA and features an improved audio frequency range compared with other Genesis horns. This results in excellent sound penetration through walls and a clear warning of danger. Horn only models may be configured for either coded or non-coded notification appliance circuits. They can also be set for high or low dBA output. This setting reduces horn output by about 6 dBA.

The suggested sound pressure level for each signaling zone used with alarm signals is at least 15 dBA above the average ambient sound level, or 5 dBA above the maximum sound level having a duration of at least 60 seconds, whichever is greater. These values are measured at five feet (1.5 m) above the floor. The average ambient sound level is A-weighted, fast response sound pressure measured over a 24-hour period.


Doubling the distance from the signal to the ear will theoretically result in a 6 dBA reduction of the received sound pressure level. The actual effect depends on the acoustic environment in the space. A 3 dBA difference represents a barely noticeable change in volume.

Installation

Genesis EGC horns and strobes mount to the required GP10 room side wiring plate. The GP10 mounting plate is included with the device for convenient pre-installing and pre-wiring. The device can be removed easily from the room side wiring plate by pushing up with a screwdriver. The cover can also be removed from the device easily with a screwdriver to access the light and sound output settings and a diagnostics test port for voltage testing.




Genesis LED EGC Series horns, strobes, and horn-strobes mount to any standard one-gang, two-gang, 4-inch octagon, and 4-inch square electrical box. Matching optional EGCT trim rings are available to cover oversized openings. Optional color matched double-gang surface boxes are also available. Genesis LED EGC series are listed to be both wall mounted or ceiling mounted.




- (1) Electrical Box
- (2) Trim Plate (optional)
- (3) Wiring plate (required, included with device)
- (4) Machine screw (2X, supplied with wiring plate)
- (5) EGC signaling appliance

Wiring




Dimensions


EGC Notification Appliances



EGCT Trim Plate (optional)



Diagnostics



Field Configuration


Temporal horn and horn-strobe models are factory set to sound in a three-pulse temporal pattern. By sliding the tone selector switch, horn only models may be configured for constant horn output that can be coded at precise intervals by KIDDE control panels and control modules.

Note: Temporal 3 coding is the required output for fire notification devices per NFPA 72. Any device coding other than temporal 3 is at the discretion and approval of the local authority having jurisdiction (AHJ).

Horns and horn-strobes are factory set for high dB output. Low dB output may be selected by sliding the tone selector switch. This reduces the output by about 6 dBA.

Genesis LED clear strobes and horn-strobes may be set for 15, 30, 75, or 115 candela output. The output setting is changed by simply removing the cover and sliding the candela switch to the desired setting. The device does not have to be removed from the wall to change the output setting. The setting remains visible through a small window on the device after the cover is closed.

Light and Sound Output Settings



Operating current

	Horns				
	Sound setting	16 to 33 VDC	16 to 33 VFWR		
-	C-Low, T-Low	20 mA	25 mA		
	C-High, T-High	30 mA	40 mA		

Strobe setting	16 to 33 VDC	16 to 33 VFWR
15, 30, 75, 115	35 mA	45 mA

Horn-Strobes

Strobe setting	Sound setting	16 to 33 VDC	16 to 33 VFWR
15, 30,	C-Low, T-Low	50 mA	60 mA
75, 115	C-High, T-High	60 mA	75 mA

Strobes

Sound Output

Horn & Horn-Strobe

Sound setting	Reverberant (UL464)	Anechoic (CAN/ULC - 5925)
C-Low, T-Low	80 dBA	86 dBA
C-High, T-High	86 dBA	92 dBA


Sound pattern - Horn Models (ULC)

Axis	Angle (°)	Output (dBA)
Horizontal	115 and 55	93.3
Vertical	125 and 50	91.7

Sound pattern - Horn-Strobe Models (ULC)

Axis	Angle (°)	Output (dBA)
Horizontal -	145 and 35	93.0
HONZONIAI -	155 and 35	90.8
Vertical -	135 and 35	92.0
verticai -	155 and 25	85.4

Light Distribution



Specifications

Operating voltage	16 to 33 VDC, 16 to 33 VFWR	
Horn signal type	Constant or TC3 temporal	
Light output	15, 30, 75, or 115 candela	
Strobe flash rate 1 fps (flash per second) approx.		
Synchronization	$20~\Omega$ max. between any two devices. To determine allowed wire resistance, refer to these specifications, and the specifications for the synchronized signal source.	
Synchronization Sources	Kidde CC Series Signal Modules, Booster and Auxiliary Power Supplies, Intelligent and Conventional Control Panels	
Wire size	12 to 18 AWG (0.75 to 2.50 mm ²)	
Mounting	Wall or Ceiling mount	
Dimensions (Ø × D)	6.8 × 1.82 in. (17.27 × 4.62 cm)	
Strobe-to-box center offset	-1.70 inches (-4.32 cm)	
Compatible electrical boxes [1]	1-gang, 2-gang, 4-inch octagon, 4-inch square	
Trim plates	EGCTR, EGCTW 10.6 × 0.3 in. (26.92 × 0.76 cm)	
Operating environment		
Temperature	32 to 122°F (0 to 50°C)	
Relative humidity	0 to 93% noncondensing	
Storage Temperature	-40 to 158 F (-40 to 70 C)	

^[1] Electrical boxes must be at least 1-1/2 in. (3.81 cm) deep.

Ordering Information

Ordoning information			
Notification Appliances		Color	Marking
FIRE	EGCARF	Red	FIRE
Horns	EGCAWF	White	FIRE
	EGCVRF	Red	FIRE
	EGCVRN	Red	None
	EGCVWF	White	FIRE
Strobes	EGCVWN	White	None
	EGCAVRF	Red	FIRE
FIRE	EGCAVRN	Red	None
	EGCAVWF	White	FIRE
Horn-strobes	EGCAVWN	White	None

Replacement Ap	opliance Covers	Color	Marking		
	EGCARF-CVR	Red	FIRE		
FIRE	EGCAWA-CVR	White	ALERT		
	EGCAWF-CVR	White	FIRE		
Horn Covers	EGCAWN-CVR	White	None		
FIRE	EGCVRF-CVR	Red	FIRE		
	EGCVWA-CVR	White	ALERT		
Harry .	EGCVWF-CVR	White	FIRE		
Strobe Covers	EGCVWN-CVR	White	None		
AIR.	EGCAVRF-CVR	Red	FIRE		
	EGCAVWA-CVR	White	ALERT		
Harry .	EGCAVWF-CVR	White	FIRE		
Horn-strobe Covers	EGCAVWN-CVR	White	None		

Accessories



GP10

Room Side Wiring Plate (required, included with device)



EGCTR

Trim plate, EGC Series, red



EGCTW

Trim plate, EGC Series, white


27193-21

Two-gang surface mount box, red


27193-26

Two-gang surface mount box, white

Model Number Syntax, Appliances



Model Number Syntax, Replacement Covers





Technology that saves lives

Contact us...

Email: kidde.fire@fs.utc.com Web: kidde.com/engineeredsystems

1016 Corporate Park Drive Mebane, NC 27302

Kidde is a registered mark in the United States and other countries.

© 2019 Walter Kidde Portable Equipment. All rights reserved.